









## System 3000 Bedieneinsatz 2fach



| Spezifikation   | Bestell-Nr. | VE  | EUR/Stück o. MWSt. | PS | EAN           |
|---|-------------|-----|--------------------|----|---------------|
|  Cremeweiß glänzend    | 5362 01     | 1/5 | 42,26              | 02 | 4010337063841 |
|  Reinweiß glänzend   | 5362 03     | 1/5 | 42,26              | 02 | 4010337063858 |
|  Reinweiß seidenmatt | 5362 27     | 1   | 42,26              | 02 | 4010337063896 |
|  Anthrazit           | 5362 28     | 1/5 | 45,14              | 02 | 4010337063902 |
|  Farbe Alu           | 5362 26     | 1   | 49,71              | 02 | 4010337063889 |
|  Schwarz matt        | 5362 005    | 1/5 | 49,71              | 02 | 4010337063919 |
|  Grau matt           | 5362 015    | 1/5 | 49,71              | 02 | 4010337087229 |
|  Edelstahl           | 5362 600    | 1   | 57,97              | 02 | 4010337063926 |

### Technische Daten

Umgebungstemperatur: -20 °C bis +45 °C