








## System 106 Rufaste beschreibbar



| Spezifikation   | Bestell-Nr. | VE | EUR/Stück o. MWSt. | PS | EAN           |
|---|-------------|----|--------------------|----|---------------|
|  Edelstahl                 | 5549 920    | 1  | 51,00              | 20 | 4010337022800 |
|  Aluminium               | 5549 926    | 1  | 39,22              | 20 | 4010337022794 |
|  Verkehrsweiß (lackiert) | 5549 902    | 1  | 34,43              | 20 | 4010337022787 |
|  Edelstahl V4A           | 5549 914    | 1  | 69,08              | 20 | 4010337092056 |
|  Bronze                  | 5549 921    | 1  | 69,08              | 20 | 4010337100928 |
|  Schwarz matt            | 5549 925    | 1  | 69,08              | 20 | 4010337100768 |

### Hinweise

- Dieses Produkt kann ausschließlich über den Gira Beschriftungsservice bestellt werden.
- Professionelle Beschriftung über den Gira Beschriftungsservice [www.beschriftung.gira.de](http://www.beschriftung.gira.de).

### Lieferumfang

- Inkl. individueller Laserbeschriftung.

## Abmessungen in mm

H 25,3

B 105,5

---