







## Taster 10 AX 250 V~ mit gerade stehender Wippe mit Kontrollfenster Wechsler 1-polig



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Reinweiß glänzend	0120 201	1/5	15,04	11	4010337065982
 Reinweiß seidenmatt	0120 27	1	15,04	01	4010337029465
 Anthrazit	0120 28	1	15,57	11	4010337029489
 Farbe Alu	0120 26	1	17,91	11	4010337029472
 Schwarz matt	0120 005	1	17,91	11	4010337037927
 Edelstahl	0120 600	1/5	22,85	11	4010337021247

### Technische Daten

Einbautiefe: 28 mm

### Hinweise

- Auch beleuchtet anschließbar.