







**Tast-Kontrollschalter 10 AX 250 V~ mit gerade stehender Wippe
Universal-Aus-Wechselschalter**



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Reinweiß glänzend	0124 201	1/5	26,18	01	4010337052715
 Reinweiß seidenmatt	0124 27	1/5	26,18	01	4010337029403
 Anthrazit	0124 28	1/5	26,59	11	4010337029427
 Farbe Alu	0124 26	1	28,96	11	4010337029410
 Schwarz matt	0124 005	1	28,96	11	4010337037958
 Edelstahl	0124 600	1	34,38	11	4010337021230

Technische Daten

Einbautiefe:	28 mm
Anschlussquerschnitt - für Leiter bis:	2,5 mm ²
Nennleistung - LEDi/ CFLi:	100 W

Hinweise

- Auch beleuchtet anschließbar.

Lieferumfang

- Glimmlampenelement 230 V~, 1,5 mA ist im Lieferumfang enthalten.
