

## Tastschalter 10 AX 250 V~ mit Abdeckung und Wippe Universal-Aus-Wechselschalter



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Reinweiß	0126 40	1/5	21,41	01	4010337126409
 Grau	0126 42	1/5	21,41	11	4010337126423
 Rot	0126 43	1/5	21,41	11	4010337126430
 Blau	0126 46	1/5	21,41	11	4010337126461
 Schwarz	0126 47	1/5	21,41	11	4010337126478

### Technische Daten

Einbautiefe:	28 mm
Anschlussquerschnitt - für starre und flexible Leiter bis:	2,5 mm <sup>2</sup>
Nennleistung - LEDi/ CFLi:	100 W

### Hinweise

- Soll dieser Schalter beleuchtet werden, bitte Kontrollschalter vorsehen.