










**Tastenschalter 10 AX 250 V~ mit Wippe 2fach  
Wechselschalter 2fach**



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Cremeweiß glänzend	0128 01	1/5	35,99	01	4010337128014
 Reinweiß glänzend	0128 03	1/5	35,99	01	4010337128038
 Reinweiß seidenmatt	0128 27	1/5	35,99	01	4010337128274
 Anthrazit	0128 28	1/5	36,46	11	4010337128281
 Farbe Alu	0128 26	1/5	39,34	11	4010337128267
 Schwarz matt	0128 005	1/5	39,34	11	4010337038030
 Grau matt	0128 015	1/5	39,34	11	4010337077176
 Edelstahl	0128 600	1/5	45,63	11	4010337021797

**Technische Daten**

Einbautiefe  
- 0125 ...: 28 mm

- 0128 ...:	32 mm
Anschlussquerschnitt - für starre und flexible Leiter bis:	2,5 mm <sup>2</sup>
Nennleistung - LEDi/ CFLi:	100 W

---