









**Tastschalter 10 AX 250 V~ mit Wippe 2fach
Wechselschalter 2fach**



| Spezifikation | Bestell-Nr. | VE | EUR/Stück o. MWSt. | PS | EAN |
|---|-------------|-----|--------------------|----|---------------|
|  Cremeweiß glänzend | 0128 01 | 1/5 | 40,02 | 01 | 4010337128014 |
|  Reinweiß glänzend | 0128 03 | 1/5 | 40,02 | 01 | 4010337128038 |
|  Reinweiß seidenmatt | 0128 27 | 1/5 | 40,02 | 01 | 4010337128274 |
|  Anthrazit | 0128 28 | 1/5 | 40,54 | 11 | 4010337128281 |
|  Farbe Alu | 0128 26 | 1/5 | 43,74 | 11 | 4010337128267 |
|  Schwarz matt | 0128 005 | 1/5 | 43,74 | 11 | 4010337038030 |
|  Grau matt | 0128 015 | 1/5 | 43,74 | 11 | 4010337077176 |
|  Edelstahl | 0128 600 | 1/5 | 50,74 | 11 | 4010337021797 |

Technische Daten

Einbautiefe
- 0125 ...: 28 mm

| | |
|---|---------------------|
| - 0128 ...: | 32 mm |
| Anschlussquerschnitt - für starre und flexible Leiter bis: | 2,5 mm ² |
| Nennleistung - LEDi/ CFLi: | 100 W |

Hinweise

- Lieferfähigkeit vorausgesetzt.
