







SCHUKO-Steckdose 16 A 250 V~ mit Kontrolllicht



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Reinweiß	0182 40	1/5	21,32	01	4010337182405
 Grau	0182 42	1/5	21,32	11	4010337182429
 Rot	0182 43	1/5	21,32	11	4010337182436
 Grün	0182 45	1	21,32	11	4010337182450
 Blau	0182 46	1/5	21,32	11	4010337182467
 Schwarz	0182 47	1/5	21,32	11	4010337182474

Merkmale

- Mit Schraubklemmen.

Technische Daten

Einbautiefe: 32 mm
Anschlussquerschnitt
- für Leiter von: 1,5 mm² bis 2,5 mm²

Hinweise

- Mit erhöhtem Anpressdruck des Erdungsbügels geprüft nach T.N.O.
