

SCHUKO-Steckdose 16 A 250 V~



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Cremeweiß glänzend	0188 01	10/100	5,26	21	4010337188018
 Reinweiß glänzend	0188 03	10/100	5,26	21	4010337188032
 Reinweiß seidenmatt	0188 27	10/100	5,26	21	4010337188278
 Anthrazit	0188 28	10/100	6,54	11	4010337188285
 Farbe Alu	0188 26	10/100	9,97	11	4010337188261
 Schwarz matt	0188 005	10/100	9,97	11	4010337037491
 Grau matt	0188 015	10/100	9,97	11	4010337077275
 Edelstahl	0188 600	1/5	16,16	11	4010337021872
 Bronze / Schwarz	0188 603	1/5	16,80	11	4010337106173



Bronze / Cremeweiß

0188 613

1/5

16,80

11

4010337106197



Messing / Schwarz

0188 604

1/5

16,80

11

4010337088462



Messing / Cremeweiß

0188 614

1/5

16,80

11

4010337106210



Chrom / Schwarz

0188 605

1/5

16,80

11

4010337000938



Chrom / Cremeweiß

0188 615

1/5

16,80

11

4010337000945

Technische Daten

Einbautiefe: 32 mm

Anschlussquerschnitt
- für Leiter von: 1,5 mm² bis 2,5 mm²

Hinweise

- Mit erhöhtem Anpressdruck des Erdungsbügels geprüft nach T.N.O.