







## Abdeckrahmen Gira Flächenschalter Reinweiß glänzend



| Spezifikation   | Bestell-Nr. | VE  | EUR/Stück o. MWSt. | PS | EAN           |
|---|-------------|-----|--------------------|----|---------------|
|  1fach                  | 0211 112    | 10  | 7,80               | 01 | 4010337043973 |
|  2fach                 | 0212 112    | 10  | 13,77              | 01 | 4010337044017 |
|  2fach ohne Mittelsteg | 1002 112    | 10  | 13,77              | 01 | 4010337047094 |
|  3fach                 | 0213 112    | 1/5 | 22,23              | 01 | 4010337044031 |
|  4fach                 | 0214 112    | 1/5 | 35,78              | 01 | 4010337044055 |
|  5fach                 | 0215 112    | 1/5 | 54,65              | 01 | 4010337044079 |

### Merkmale

- Bruchsicher.

### Hinweise

- In Verbindung mit Dichtungsflansch auch für die Montage wassergeschützt Unterputz IP44 geeignet.