










Wippe



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Cremeweiß glänzend	0296 01	10	3,06	21	4010337296010
 Reinweiß glänzend	0296 03	10	3,06	21	4010337296034
 Reinweiß seidenmatt	0296 27	10/100	3,06	21	4010337296270
 Anthrazit	0296 28	10	3,61	11	4010337296287
 Farbe Alu	0296 26	10	6,04	11	4010337296263
 Schwarz matt	0296 005	10	6,04	11	4010337038061
 Grau matt	0296 015	10	6,04	11	4010337080220
 Edelstahl	0296 600	10	11,39	11	4010337021667
 Bronze	0296 603	10	11,86	11	4010337097747



Messing

0296 604

10

11,86

11

4010337097754



Chrom

0296 605

10

11,86

11

4010337001416

Hinweise

- Abdeckrahmen (1- bis 5fach) aus den Schalterprogrammen Standard 55 und Gira E2 in Verbindung mit dem Dichtungsset auch für die Installation von Wippschalter und Wipptaster wassergeschützt IP44 geeignet (gilt nicht für Wippe 2fach).