







## Stereolautsprecher-Steckdose



| Spezifikation   | Bestell-Nr. | VE  | EUR/Stück o. MWSt. | PS | EAN           |
|---|-------------|-----|--------------------|----|---------------|
|  Cremeweiß glänzend    | 0402 01     | 1/5 | 18,71              | 01 | 4010337402015 |
|  Reinweiß glänzend   | 0402 03     | 1/5 | 18,71              | 01 | 4010337402039 |
|  Reinweiß seidenmatt | 0402 27     | 1/5 | 18,71              | 01 | 4010337402275 |
|  Anthrazit           | 0402 28     | 1/5 | 21,31              | 11 | 4010337402282 |
|  Farbe Alu           | 0402 26     | 1/5 | 23,96              | 11 | 4010337402268 |
|  Schwarz matt        | 0402 005    | 1/5 | 23,96              | 11 | 4010337037880 |

### Merkmale

- Mit Schraubklemmen.

### Technische Daten

|                            |                     |
|----------------------------|---------------------|
| Einbautiefe:               | 31 mm               |
| Anschlussquerschnitt max.: | 1,5 mm <sup>2</sup> |

## Hinweise

- Für Leitungsquerschnitt bis max. 10 mm<sup>2</sup>.
  - Als Einsatz für High-End-Lautsprechersteckverbinder (WBT) und Datenhaube verwenden.
-