










Lautsprecher Unterputz-Radio



| Spezifikation | Bestell-Nr. | VE | EUR/Stück o. MWSt. | PS | EAN |
|---|-------------|----|--------------------|----|---------------|
|  Cremeweiß glänzend | 2282 01 | 1 | 27,64 | 03 | 4010337076230 |
|  Reinweiß glänzend | 2282 03 | 1 | 27,64 | 03 | 4010337076247 |
|  Reinweiß seidenmatt | 2282 27 | 1 | 27,64 | 03 | 4010337076254 |
|  Anthrazit | 2282 28 | 1 | 29,76 | 03 | 4010337076261 |
|  Farbe Alu | 2282 26 | 1 | 32,42 | 03 | 4010337076162 |
|  Schwarzglasoptik | 2282 05 | 1 | 37,20 | 03 | 4010337889182 |
|  Schwarz matt | 2282 005 | 1 | 32,42 | 03 | 4010337037286 |
|  Grau matt | 2282 015 | 1 | 32,42 | 03 | 4010337083931 |
|  Edelstahl | 2282 600 | 1 | 37,20 | 03 | 4010337032861 |

Merkmale

- Lautsprecher zum Anschluss an das Gira Unterputz-Radio.

Technische Daten

| | |
|--|---------------------|
| Einbautiefe: | 32 mm |
| Anschlussquerschnitt - Lautsprecher-/AUX-Anschluss: | 1,5 mm ² |
| Impedanz: | 8 Ω |
| Umgebungstemperatur: | -5 °C bis +50 °C |
