










Lautsprecher Unterputz-Radio RDS



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Cremeweiß glänzend	2282 01	1	31,35	03	4010337076230
 Reinweiß glänzend	2282 03	1	31,35	03	4010337076247
 Reinweiß seidenmatt	2282 27	1	31,35	03	4010337076254
 Anthrazit	2282 28	1	33,11	03	4010337076261
 Farbe Alu	2282 26	1	35,77	03	4010337076162
 Schwarzglasoptik	2282 05	1	40,75	03	4010337889182
 Schwarz matt	2282 005	1	40,78	11	4010337037286
 Grau matt	2282 015	1	37,34	11	4010337083931
 Edelstahl	2282 600	1	40,75	03	4010337032861

Merkmale

- Lautsprecher zum Anschluss an das Gira Unterputz-Radio RDS.

Technische Daten

Einbautiefe:	32 mm
Anschlussquerschnitt - Lautsprecher-/AUX-Anschluss:	1,5 mm ²
Umgebungstemperatur:	-5 °C bis +50 °C
