






Wippschalter 3fach 10 AX 250 V~ mit Wippen Universal-Aus-Wechselschalter



| Spezifikation | Bestell-Nr. | VE | EUR/Stück o. MWSt. | PS | EAN |
|--|-------------|------|--------------------|----|---------------|
|  Cremeweiß glänzend | 2832 01 | 1/10 | 36,52 | 29 | 4010337832010 |
|  Reinweiß glänzend | 2832 03 | 1/10 | 36,52 | 29 | 4010337832034 |
|  Anthrazit | 2832 28 | 1/10 | 39,25 | 29 | 4010337832287 |
|  Farbe Alu | 2832 26 | 1/10 | 43,42 | 29 | 4010337832263 |
|  Schwarz matt | 2832 005 | 1/10 | 43,42 | 11 | 4010337038528 |
|  Grau matt | 2832 015 | 1/10 | 43,42 | 11 | 4010337087120 |
|  Edelstahl (lackiert) | 2832 600 | 1/10 | 47,29 | 29 | 4010337022053 |

Technische Daten

| | |
|---|---------------------|
| Einbautiefe: | 25 mm |
| Anschlussquerschnitt - für Leiter bis: | 2,5 mm ² |

Hinweise

- Nur für Schraubbefestigung.
