








Wipp-Kontrollschalter British Standard (BS EN 60669-1) 20 AX 250 V~mit Wippe Ausschalter 2-polig



| Spezifikation | Bestell-Nr. | VE | EUR/Stück o. MWSt. | PS | EAN |
|---|-------------|------|--------------------|----|---------------|
|  Cremeweiß glänzend | 2834 01 | 1/10 | 46,92 | 29 | 4010337078814 |
|  Reinweiß glänzend | 2834 03 | 1/10 | 46,92 | 29 | 4010337078821 |
|  Anthrazit | 2834 28 | 1/10 | 47,43 | 29 | 4010337078845 |
|  Farbe Alu | 2834 26 | 1/10 | 50,54 | 29 | 4010337078838 |
|  Schwarz matt | 2834 005 | 1/10 | 50,54 | 29 | 4010337038573 |
|  Grau matt | 2834 015 | 1/10 | 50,54 | 29 | 4010337087137 |
|  Edelstahl | 2834 600 | 1/10 | 57,72 | 29 | 4010337022305 |

Technische Daten

| | |
|---|--|
| Einbautiefe: | 24 mm |
| Anschlussquerschnitt - für Leiter bis: | 2 x 4 mm ² oder 1 x 6 mm ² |

Hinweise

- Nur für Schraubbefestigung.
 - BS EN 60669-1.
-