

## SCHUKO-Steckdose 16 A 250 V~ mit Aufdruck "EDV" System 55



| Spezifikation                                                                                               | Bestell-Nr. | VE  | EUR/Stück o. MWSt. | PS | EAN           |
|-------------------------------------------------------------------------------------------------------------|-------------|-----|--------------------|----|---------------|
|  Cremeweiß glänzend        | 4458 01     | 1/5 | 9,33               | 01 | 4010337093176 |
|  Reinweiß glänzend       | 4458 03     | 1/5 | 9,33               | 01 | 4010337093190 |
|  Reinweiß seidenmatt     | 4458 27     | 1/5 | 9,33               | 01 | 4010337093213 |
|  Anthrazit               | 4458 28     | 1/5 | 10,68              | 11 | 4010337093220 |
|  Farbe Alu (lackiert)    | 4458 26     | 1/5 | 15,52              | 11 | 4010337093206 |
|  Schwarz matt (lackiert) | 4458 005    | 1/5 | 15,52              | 11 | 4010337093169 |
|  Grau matt (lackiert)    | 4458 015    | 1/5 | 15,52              | 11 | 4010337093183 |

### Technische Daten

|                                           |                     |
|-------------------------------------------|---------------------|
| Einbautiefe:                              | 32 mm               |
| Leitergut:                                | starr und flexibel  |
| Anschlussquerschnitt<br>- für Leiter von: | 1,5 mm² bis 2,5 mm² |

## Hinweise

- Mit erhöhtem Anpressdruck des Erdungsbügels geprüft nach T.N.O.

---