











Wippe für Wippenet 2fach für Tastsensor 4



Spezifikation	Bestell-Nr.	VE	EUR/Stück o. MWSt.	PS	EAN
 Aluminium Reinweiß glänzend (lackiert)	8332 903	1	55,07	06	4010337098713
 Aluminium Reinweiß seidenmatt (lackiert)	8332 927	1	55,07	06	4010337098737
 Aluminium Anthrazit (lackiert)	8332 928	1	55,07	06	4010337098676
 Aluminium (eloxiert)	8332 17	1	43,48	06	4010337096979
 Aluminium Schwarz matt (lackiert)	8332 905	1	55,07	06	4010337098690
 Aluminium Grau matt (lackiert)	8332 915	1	55,07	06	4010337098652
 Aluminium Schwarz (eloxiert)	8332 126	1	43,48	06	4010337096993
 Bronze	8332 38	1	92,75	06	4010337098751
 Glas Weiß	8332 12	1	43,48	06	4010337097792

	Glas Schwarz	8332 05	1	43,48	06	4010337098027
	Edelstahl	8332 219	1	75,36	06	4010337097334