










Wippe für Wippenet 2fach für Tastsensor 4.95



| Spezifikation | Bestell-Nr. | VE | EUR/Stück o. MWSt. | PS | EAN |
|--|-------------|----|--------------------|----|---------------|
|  Aluminium Reinweiß glänzend (lackiert) | 8332 903 | 1 | 55,07 | 06 | 4010337098713 |
|  Aluminium Reinweiß seidenmatt (lackiert) | 8332 927 | 1 | 55,07 | 06 | 4010337098737 |
|  Aluminium Anthrazit (lackiert) | 8332 928 | 1 | 55,07 | 06 | 4010337098676 |
|  Aluminium (eloxiert) | 8332 17 | 1 | 43,48 | 06 | 4010337096979 |
|  Aluminium Schwarz matt (lackiert) | 8332 905 | 1 | 55,07 | 06 | 4010337098690 |
|  Aluminium Grau matt (lackiert) | 8332 915 | 1 | 55,07 | 06 | 4010337098652 |
|  Aluminium Schwarz (eloxiert) | 8332 126 | 1 | 43,48 | 06 | 4010337096993 |
|  Bronze | 8332 38 | 1 | 92,75 | 06 | 4010337098751 |
|  Glas Weiß | 8332 12 | 1 | 43,48 | 06 | 4010337097792 |

| | | | | | | |
|---|--------------|----------|---|-------|----|---------------|
|  | Glas Schwarz | 8332 05 | 1 | 43,48 | 06 | 4010337098027 |
|  | Edelstahl | 8332 219 | 1 | 75,36 | 06 | 4010337097334 |