







**Button 10 A 250 V~ with upright rocker with control window
2-way momentary contact, 1-pole**



Specification	Order No.	Packing unit	PS	EAN
 pure white glossy	0120 201	1/5	11	4010337065982
 pure white matt	0120 27	1/5	01	4010337029465
 anthracite	0120 28	1/5	11	4010337029489
 colour aluminium	0120 26	1/5	11	4010337029472
 black matt	0120 005	1/5	11	4010337037927
 stainless steel	0120 600	1/5	11	4010337021247

Technical data

Installation depth:	28 mm
Connection cross section - For rigid and flexible conductors up to:	2.5 mm ²

Notes

- Can also be connected to be illuminated.

- Subject to availability.
