




**Pushbutton switch 10 AX 250 V~with upright rocker  
Universal 1-way/2-way switch**



Specification	Order No.	Packing unit	PS	EAN
 pure white glossy	0121 201	1/5	01	4010337052692
 pure white matt	0121 27	1/5	01	4010337029311
 anthracite	0121 28	1/5	11	4010337029335
 colour aluminium	0121 26	1	11	4010337029328
 black matt	0121 005	1	11	4010337037972
 grey matt	0121 015	1	11	4010337077091
 stainless steel	0121 600	1/5	11	4010337021261

**Technical data**

Installation depth:	28 mm
Connection cross section - For rigid and flexible conductors up to:	2.5 mm <sup>2</sup>
Rated output - LEDi/CFLi:	100 W

---

## Notes

- Subject to availability.

---