


**Pushbutton indicator switch 10 AX 250 V~ with rocker  
Circuit breaker, 2-pole**



| Specification  | Order No. | Packing unit | PS | EAN           |
|--|-----------|--------------|----|---------------|
|  pure white glossy | 0122 112  | 1/5          | 01 | 4010337043782 |

#### Technical data

|  |                     |
|--|---------------------|
| Installation depth:  | 28 mm               |
| Connection cross section<br>- For rigid and flexible conductors up to: | 2.5 mm <sup>2</sup> |
| Rated output<br>- LEDi/CFLi:   | 100 W               |

#### Notes

- Can also be connected to be illuminated.
- Subject to availability.

#### Scope of supply

- A neon lamp element 230 V~, 1.5 mA is included in the scope of supply.