




**Pushbutton indicator switch 10 AX 250 V~ with rocker
Circuit breaker, 2-pole**



| Specification | Order No. | Packing unit | PS | EAN |
|---|-----------|--------------|----|---------------|
|  cream white glossy | 0122 01 | 1/5 | 01 | 4010337122012 |
|  pure white glossy | 0122 03 | 1/5 | 01 | 4010337122036 |
|  pure white matt | 0122 27 | 1/5 | 01 | 4010337122272 |
|  anthracite | 0122 28 | 1/5 | 11 | 4010337122289 |
|  colour aluminium | 0122 26 | 1/5 | 11 | 4010337122265 |
|  black matt | 0122 005 | 1/5 | 11 | 4010337037934 |
|  stainless steel | 0122 600 | 1/5 | 11 | 4010337021773 |

Technical data

| | |
|--|---------------------|
| Installation depth: | 28 mm |
| Connection cross section - For rigid and flexible conductors up to: | 2.5 mm ² |
| Rated output - LEDi/CFLi: | 100 W |

Notes

- Can also be connected to be illuminated.
 - Subject to availability.
-

Scope of supply

- A neon lamp element 230 V~, 1.5 mA is included in the scope of supply.
-