










**Pushbutton switch, 10 AX 250 V~ with rocker, 2-gang
Series switch**



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	0125 01	1/5	01	4010337125013
 pure white glossy	0125 03	1/5	01	4010337125037
 pure white matt	0125 27	1/5	01	4010337125273
 anthracite	0125 28	1/5	11	4010337125280
 colour aluminium	0125 26	1/5	11	4010337125266
 black matt	0125 005	1/5	11	4010337038016
 grey matt	0125 015	1/5	11	4010337077138
 stainless steel	0125 600	1/5	11	4010337021780
 bronze	0125 603	1/5	11	4010337106012



brass

0125 604

1/5

11

4010337106029



chrome

0125 605

1/5

11

4010337000839

Technical data

Installation depth

- 0125 ...:

28 mm

- 0128 ...:

32 mm

Connections

- for conductors up to:

2.5 mm²
