









**Pushbutton switch 10 AX 250 V~ with rocker, 2-gang  
Series switch**



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	0125 01	1/5	01	4010337125013
 pure white glossy	0125 03	1/5	01	4010337125037
 pure white matt	0125 27	1/5	01	4010337125273
 anthracite	0125 28	1/5	11	4010337125280
 colour aluminium	0125 26	1/5	11	4010337125266
 black matt	0125 005	1/5	11	4010337038016
 grey matt	0125 015	1/5	11	4010337077138
 stainless steel	0125 600	1/5	11	4010337021780

**Technical data**

Installation depth  
- 0125 ...: 28 mm

# GIRA Data sheet

catalogue.gira.com

© Copyright by  
Gira Giersiepen GmbH & Co. KG  
All rights reserved

www.gira.com

- 0128 ...:	32 mm
Connection cross section	
- For rigid and flexible conductors up to:	2.5 mm <sup>2</sup>
Rated output	
- LEDi/CFLi:	100 W

---

## Notes

- Subject to availability.

---