




**Pushbutton switch 10 AX 250 V~ with rocker
Universal 1-way/2-way switch**



| Specification | Order No. | Packing unit | PS | EAN |
|--|-----------|--------------|----|---------------|
|  pure white | 0126 66 | 1/5 | 13 | 4010337126669 |
|  anthracite | 0126 67 | 1/5 | 13 | 4010337126676 |
|  colour aluminium | 0126 65 | 1/5 | 13 | 4010337126652 |

Technical data

| | |
|--|---------------------|
| Installation depth: | 28 mm |
| Connection cross section | |
| - For rigid and flexible conductors up to: | 2.5 mm ² |
| Rated output | |
| - LEDi/CFLi: | 100 W |

Notes

- With touch-activation operation.
 - Theft protection by means of optional, screw-in clamp piece. This makes using wall plugs for the cover frame unnecessary.
 - If this switch is to be illuminated, please incorporate a control switch.
 - Successor item: 3126 00 + 3496 xx
- Available from 08/2024.
- Subject to availability.