










**Pushbutton switch 10 AX 250 V~ with rocker, 2-gang
2-way switch, 2-gang**



| Specification | Order No. | Packing unit | PS | EAN |
|---|-----------|--------------|----|---------------|
|  cream white glossy | 0128 01 | 1/5 | 01 | 4010337128014 |
|  pure white glossy | 0128 03 | 1/5 | 01 | 4010337128038 |
|  pure white matt | 0128 27 | 1/5 | 01 | 4010337128274 |
|  anthracite | 0128 28 | 1/5 | 11 | 4010337128281 |
|  colour aluminium | 0128 26 | 1/5 | 11 | 4010337128267 |
|  black matt | 0128 005 | 1/5 | 11 | 4010337038030 |
|  grey matt | 0128 015 | 1/5 | 11 | 4010337077176 |
|  stainless steel | 0128 600 | 1/5 | 11 | 4010337021797 |

Technical data

Installation depth
- 0125 ...: 28 mm

GIRA Data sheet

catalogue.gira.com

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

| | |
|--|---------------------|
| - 0128 ...: | 32 mm |
| Connection cross section | |
| - For rigid and flexible conductors up to: | 2.5 mm ² |
| Rated output | |
| - LEDi/CFLi: | 100 W |

Notes

- Subject to availability.
-