


**Pushbutton switch 10 AX 250 V~ with rocker, 2-gang  
2-way switch, 2-gang**



| Specification  | Order No. | Packing unit | PS | EAN           |
|--|-----------|--------------|----|---------------|
|  pure white glossy | 0128 112  | 1/5          | 01 | 4010337043874 |

**Technical data**

Installation depth

|             |       |
|-------------|-------|
| - 0125 ...: | 28 mm |
| - 0128 ...: | 32 mm |

Connections

|  |                     |
|--|---------------------|
| - for rigid and flexible conductors up to: | 2.5 mm <sup>2</sup> |
|--|---------------------|

Rated output

|             |       |
|-------------|-------|
| - LED/ CFL: | 100 W |
|-------------|-------|