




**Pushbutton switch 10 AX 250 V~ with rocker, 2-gang  
2-way switch, 2-gang**



Specification	Order No.	Packing unit	PS	EAN
 pure white	0128 66	1	13	4010337128663
 anthracite	0128 67	1	13	4010337128670
 colour aluminium	0128 65	1	13	4010337128656

### Technical data

Installation depth

- 0125 ...:	25 mm
- 0128 ...:	28 mm

Connection cross section

- For rigid and flexible conductors up to:	2.5 mm <sup>2</sup>
--	---------------------

Rated output

- LEDi/CFLi:	100 W
--------------	-------

### Notes

- With touch-activation operation.
- Theft protection by means of optional, screw-in clamp piece. This makes using wall plugs for the cover frame unnecessary.
- Subject to availability.