










**Pushbutton indicator switch 10 AX 250 V~ with rocker
Universal off/2-way switch**



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	0136 01	1/5	01	4010337136019
 pure white glossy	0136 03	1/5	01	4010337136033
 pure white matt	0136 27	1/5	01	4010337136279
 anthracite	0136 28	1/5	11	4010337136286
 colour aluminium	0136 26	1/5	11	4010337136262
 black matt	0136 005	1/5	11	4010337037941
 grey matt	0136 015	1/5	11	4010337077190
 stainless steel	0136 600	1/5	11	4010337021766
 bronze	0136 603	1/5	11	4010337106081



brass

0136 604

1/5

11

4010337106098



chrome

0136 605

1/5

11

4010337000860

Technical data

Installation depth: 28 mm

Connections
- for conductors up to: 2.5 mm²

Notes

- Can also be connected with illumination.

Scope of supply

- Neon lamp element 230 V~, 1.5 mA is included in the scope of supply.
