









**Pushbutton indicator switch 10 AX 250 V~ with rocker  
Universal 1-way/2-way switch**



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	0136 01	1/5	01	4010337136019
 pure white glossy	0136 03	1/5	01	4010337136033
 pure white matt	0136 27	1/5	01	4010337136279
 anthracite	0136 28	1/5	11	4010337136286
 colour aluminium	0136 26	1/5	11	4010337136262
 black matt	0136 005	1/5	11	4010337037941
 grey matt	0136 015	1/5	11	4010337077190
 stainless steel	0136 600	1/5	11	4010337021766

**Technical data**

Installation depth: 28 mm

Connection cross section  
- For rigid and flexible conductors up to: 2.5 mm<sup>2</sup>

Illustrations are similar and may deviate from originals.

Rated output

- LEDi/CFLi:

100 W

---

## Notes

- Can also be connected to be illuminated.
  - Subject to availability.
- 

## Scope of supply

- A neon lamp element 230 V~, 1.5 mA is included in the scope of supply.
-