





**Pushbutton indicator switch 10 AX 250 V~ with rocker
Universal 1-way/2-way switch**



Specification	Order No.	Packing unit	PS	EAN
 pure white	0136 66	1/5	13	4010337136668
 anthracite	0136 67	1/5	13	4010337136675
 colour aluminium	0136 65	1/5	13	4010337136651

Technical data

Installation depth:	28 mm
Connection cross section - For rigid and flexible conductors up to:	2.5 mm ²
Rated output - LEDi/CFLi:	100 W

Notes

- With touch-activation operation.
- Theft protection by means of optional, screw-in clamp piece. This makes using wall plugs for the cover frame unnecessary.
- Can also be connected to be illuminated.

Scope of supply

- A neon lamp element 230 V~, 1.5 mA is included in the scope of supply.