










Socket outlets
SCHUKO socket outlet 16 A 250 V~



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	0188 01	10/100	21	4010337188018
 pure white glossy	0188 03	10/100	21	4010337188032
 pure white matt	0188 27	10/100	21	4010337188278
 anthracite	0188 28	10/100	11	4010337188285
 colour aluminium	0188 26	10/100	11	4010337188261
 black matt	0188 005	10/100	11	4010337037491
 grey matt	0188 015	10/100	11	4010337077275
 stainless steel	0188 600	1/5	11	4010337021872
 bronze + black	0188 603	1/5	11	4010337106173



bronze + cream white

0188 613

1/5

11

4010337106197



brass + black

0188 604

1/5

11

4010337088462



brass + cream white

0188 614

1/5

11

4010337106210



chrome + black

0188 605

1/5

11

4010337000938



chrome + cream white

0188 615

1/5

11

4010337000945

Technical data

Installation depth: 32 mm

Connections
- for conductors from: 1.5 mm² to 2.5 mm²
