







## Gira F100 cover frame pure white glossy



| Specification   | Order No. | Packing unit | PS | EAN           |
|---|-----------|--------------|----|---------------|
|  1-gang                    | 0211 112  | 10/100       | 01 | 4010337043973 |
|  2-gang                  | 0212 112  | 10/100       | 01 | 4010337044017 |
|  2-gang without crossbar | 1002 112  | 10           | 01 | 4010337047094 |
|  3-gang                  | 0213 112  | 1/5          | 01 | 4010337044031 |
|  4-gang                  | 0214 112  | 1/5          | 01 | 4010337044055 |
|  5-gang                  | 0215 112  | 1/5          | 01 | 4010337044079 |

### Features

- Shatter-proof.

### Notes

- In conjunction with a sealing flange, also suitable for installation as water-protected flush-mounted IP44.