








Gira E2 cover frame anthracite



| Specification | Order No. | Packing unit | PS | EAN |
|--|-----------|--------------|----|---------------|
|  1-gang | 0211 23 | 10/100 | 11 | 4010337211235 |
|  1.5-gang | 1001 23 | 10 | 11 | 4010337881339 |
|  2-gang | 0212 23 | 10/100 | 11 | 4010337212232 |
|  2-gang, without crossbar | 1002 23 | 10 | 11 | 4010337002239 |
|  3-gang | 0213 23 | 1/5 | 11 | 4010337213239 |
|  4-gang | 0214 23 | 1/5 | 11 | 4010337214236 |
|  5-gang | 0215 23 | 1/5 | 11 | 4010337215233 |

Notes

- Also suitable for duct installation.
- In connection with the sealing kit, cover frame (1-gang to 5-gang) is also suitable for installation as water-protected flush-mounted IP44.