


## LED dimming insert with rotary on/off switch



Specification	Order No.	Packing unit	PS	EAN
 20 – 200 W	0300 00	1/5	22	4010337300007

### Features

- Switching and dimming of light bulbs, HV halogen lamps and leading edge dimmable HV LED lamps.
- Short-circuit protection using micro-fuse.
- With screw terminals.

### Technical data

Rated voltage:	AC 230 V, 50 Hz
Connected load at 25 °C	
- HV LED lamps (leading edge):	typically 3 to 40 W
- Light bulbs:	20 to 200 W
- HV halogen lamps:	20 to 200 W
Installation depth:	32 mm
Connections	
- maximum:	1 x 2.5 mm <sup>2</sup>
- minimum:	1 x 0.5 mm <sup>2</sup>
Ambient temperature:	-5 °C to +45 °C

### Notes

- If the ambient temperature is higher than 25 °C, the connected load must be reduced.