


Electronic potentiometer insert for 1–10 V control input Button function



Specification	Order No.	Packing unit	PS	EAN
	0308 00	1/5	02	4010337308003

Features

- Electronic potentiometer with button function (in combination with remote-control switches only) for electronic ballasts or Tronic transformers with 1 – 10 V control input.
- Pressing the operating knob sends an impulse to the remote-control switch and switches the electronic ballasts on and off.
- Rotating adjusts the brightness.

Technical data

Rated voltage:	AC 230 V, 50/60 Hz
1 – 10 V interface	
- Control voltage:	0.5 to 10 V
- Control current:	max. 50 mA
Ohmic switching current:	2 A
Installation depth:	32 mm
Connections	
- maximum:	4 mm ²
Ambient temperature:	+5 °C to +45 °C

Scope of supply

- Fuse is included in the scope of supply.