


Electronic potentiometer insert for 1 – 10 V control input Switching function



Specification	Order No.	Packing unit	PS	EAN
	0309 00	1/5	02	4010337309000

Features

- Electronic potentiometer with switching function for electronic ballasts or Tronic transformers with 1 – 10 V control input.
- Pressing the operating button switches the electronic ballasts on and off.
- Rotating adjusts the brightness.
- Basic brightness can be set.
- Short-circuit protection of the switching contact by integrated fine fuse.

Technical data

Rated voltage: AC 230 V, 50/60 Hz

1 – 10 V interface

- Control voltage: 0.7 to 12 V
- Control current: max. 50 mA

Switching current

- Ohmic: 6 A

Installation depth: 32 mm

Connection cross section

- maximum: 4 mm²

Ambient temperature: +5 °C to +25 °C

Scope of supply

- Fuse is included in the scope of supply.