


## Electronic potentiometer insert for 1–10 V control input Switching function



Specification	Order No.	Packing unit	PS	EAN
	0309 00	1/5	02	4010337309000

### Features

- Electronic potentiometer with switching function for electronic ballasts or Tronic transformers with 1 – 10 V control input.
- Pressing the operating knob switches the electronic ballasts on and off.
- Rotating adjusts the brightness.

### Technical data

Rated voltage:	AC 230 V, 50/60 Hz
1 – 10 V interface	
- Control voltage:	0.5 to 10 V
- Control current:	max. 50 mA
Switching current	
- Ohmic:	6 A
- Capacitive:	6 A (70 µF)
Installation depth:	32 mm
Connections	
- maximum:	4 mm <sup>2</sup>
Ambient temperature:	+5 °C to +45 °C

### Scope of supply

- Fuse is included in the scope of supply.