


Speed regulator insert with rotary on/off switch



Specification	Order No.	Packing unit	PS	EAN
 0,1 –2.7 A	0314 00	1/5	02	4010337314004

Features

- Speed regulator for speed control of single-phase motors such as induction motors, shaded-pole motors, and universal motors.
- Excess-temperature protection, manual restarting after cool-down.
- Switching output for slat control or for switching ohmic loads.
- With plug terminals.

Technical data

Rated voltage:	AC 230/240 V, 50/60 Hz
Rated current:	0.1 to 2.7 A
Motor current and slat current:	max. 2.7 A
Installation depth:	33 mm.
Connections	
- maximum:	2.5 mm ²
- minimum:	1.0 mm ²
Ambient temperature:	+5 °C to +25 °C

Scope of supply

- Fuse is included in the scope of supply.