


Control Unit, 1 – 10 V



Specification	Order No.	Packing unit	PS	EAN
 white	0360 00	1	02	4010337360001

Features

- Built-in control unit for switching and dimming fluorescent lamps using electronic ballast with 1–10 V control input or Gira Tronic transformers with 1–10 V control input.
- Operation is possible using mechanical push buttons.
- Bulb-saving switch-on.
- Memory function (brightness memory).

Technical data

Rated voltage:	AC 230 V, 50 Hz
Connected load of switching contact	
- Ohmic load:	2300 W
- Gira Tronic transformer:	type dependent
- Electronic ballasts:	type dependent
1 – 10 V interface	
- Control voltage:	1 to 10 V
- Control current:	max. 200 mA
Cable length	
- Control line:	max. 100 m
- Load:	max. 100 m
Auxiliary inputs:	unlimited
Connections:	max. 4 mm ²
Ambient temperature:	max. +50 °C

GIRA Data sheet

catalogue.gira.com

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

Dimensions in mm

W 175

H 42

D 18
