


Room temperature controller 24/10 (4) A~ with NC contact



Specification	Order No.	Packing unit	PS	EAN
 pure white glossy	0391 112	1/5	02	4010337065562

Technical data

Rated voltage:	AC 24 V
Rated current:	10 (4) A
Connected load:	approx. 240 W
Switching temperature differential:	approx. 0.5 K
Night-time reduction:	approx. 4 K
Energy class:	I = 1 %
Installation depth:	25 mm
Ambient temperature:	+5 °C to +30 °C

Notes

- For screw mounting only.
- Flat design.