









**Room temperature controller 230/10 (4) A~
with NO contact and sensor for electrical floor heating**



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	0394 01	1	02	4010337394013
 pure white glossy	0394 03	1	02	4010337394037
 pure white matt	0394 27	1	02	4010337394273
 anthracite	0394 28	1	02	4010337394280
 colour aluminium	0394 26	1	02	4010337394266
 black matt	0394 005	1	02	4010337037408
 grey matt	0394 015	1	02	4010337080893
 stainless steel	0394 600	1	02	4010337021537

Features

- Within one hour of continuous heating, the room temperature controller automatically interrupts the heating process for 5 minutes (the heater is switched off. Requirement of EN 50559).

Technical data

Rated voltage:	AC 230 V, 50 Hz
Rated current:	10 (4) A
Rated surge voltage:	4 kV
Connected load:	2200 W
Night-time reduction:	approx. 4 K
Energy class:	IV = 2 %
Ambient temperature:	0°C to +25°C
Solid conductor	
- Connections:	1 to 2.5 mm ²
Remote sensor	
- Connection cable:	4 m
- can be extended:	max. 50 m
- can be extended:	2 x 1.5 mm ²

Notes

- For screw mounting only.
- Flat design.
- Install remote sensor in empty tube in the floor.
- The supply cable to the remote sensor can be extended to 50 m with a 2-wire cable (2 x 1.5 mm²).

Scope of supply

- A sensor in the plastic cap is included in the scope of supply.

Dimensions in mm

Sensor:	Ø 8,5	H 40
---------	-------	------