








Room temperature controller 230/5 (2) A~ with 2-way switch



| Specification | Order No. | Packing unit | PS | EAN |
|---|-----------|--------------|----|---------------|
|  cream white glossy | 0396 01 | 1/5 | 02 | 4010337396017 |
|  pure white glossy | 0396 03 | 1/5 | 02 | 4010337396031 |
|  pure white matt | 0396 27 | 1/5 | 02 | 4010337396277 |
|  anthracite | 0396 28 | 1/5 | 02 | 4010337396284 |
|  colour aluminium | 0396 26 | 1/5 | 02 | 4010337396260 |
|  black matt | 0396 005 | 1 | 02 | 4010337056706 |
|  stainless steel | 0396 600 | 1 | 02 | 4010337021544 |

Technical data

Rated voltage: AC 230 V, 50 Hz

Rated current
 - Heating (NC contact): 10 (4) A
 - Cooling (NO contact): 5 (2) A

Connected load
 - Heating (NC contact): 2200 W

| | |
|-------------------------------------|-----------------|
| - Cooling (NO contact): | 1100 W |
| Switching temperature differential: | approx. 0.5 K |
| Energy class: | I = 1 % |
| Installation depth: | 25 mm |
| Ambient temperature: | +5 °C to +30 °C |

Notes

- For screw mounting only.
 - Flat design.
-