









Room temperature controller 230/5 (2) A~ with 2-way switch



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	0396 01	1/5	02	4010337396017
 pure white glossy	0396 03	1/5	02	4010337396031
 pure white matt	0396 27	1/5	02	4010337396277
 anthracite	0396 28	1/5	02	4010337396284
 colour aluminium	0396 26	1/5	02	4010337396260
 black matt	0396 005	1/5	02	4010337056706
 grey matt	0396 015	1/5	02	4010337080909
 stainless steel	0396 600	1/5	02	4010337021544

Technical data

Rated voltage: AC 230 V, 50 Hz

Rated current
- Heating (NC contact): 10 (4) A

Illustrations are similar and may deviate from originals.

- Cooling (NO contact):	5 (2) A
Connected load	
- Heating (NC contact):	2200 W
- Cooling (NO contact):	1100 W
Switching temperature differential:	approx. 0.5 K
Energy class:	I = 1 %
Installation depth:	25 mm
Ambient temperature:	+5 °C to +30 °C

Notes

- For screw mounting only.
 - Flat design.
-