









SCHUKO socket outlet, 16 A 250 V~ with surgeage protection and inscription space



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	0451 01	1/5	02	4010337451013
 pure white glossy	0451 03	1/5	02	4010337451037
 pure white matt	0451 27	1/5	02	4010337451273
 anthracite	0451 28	1/5	02	4010337451280
 colour aluminium	0451 26	1/5	02	4010337451266
 black matt	0451 005	1/5	02	4010337037699
 grey matt	0451 015	1/5	02	4010337080978
 red glossy	0451 02	1/5	02	4010337451020

Features

- Protects electrical and electronic devices from transient overloads.
 - With acoustic and optical signal.
 - With screw terminals.
-

Technical data

Rated voltage:	AC 230 V, 50/60 Hz
Rated current _{I_L} :	16 A
Protection level	
- U _P (L/N):	≤ 1.25 kV
- U _P (L/PE, N/PE):	≤ 1.25 kV
Installation depth:	31 mm
Ambient temperature:	-5 °C to +40 °C
Connection cross section	
- for conductors from:	1.5 mm ² to 2.5 mm ²

Notes

- Type 3 fine protection for electrical and electronic devices from transient overloads according to EN 61643-11.
 - Use only in combination with coarse protection type 1 and average protection type 2.
 - Use in TN, TT, and IT networks.
-

Scope of supply

- Inscription label "EDV" is enclosed.
-