


Bolt switching contact VdS



Specification	Order No.	Packing unit	PS	EAN
	0924 00	1	03	4010337924005

Features

- Electro-mechanical contact for closure monitoring of doors.
- Contact is inserted inaccessibly into the striking plate of the door frame and actuated by the lock bolt when the door is closed.
- Switching point of the bolt switch contact can be functionally adapted.
- With switch lever extension for adaptation to larger bolt cut-outs or special bolt shapes.

Technical data

Contact type:	2-way momentary contact
Switching voltage:	max. DC 30 V
Switching current:	max. 100 mA
Contact load:	max. 3 W/VA
Connection cable:	3 m
Protection type:	IP 67

Notes

- VdS approval G 190 008

Dimensions in mm

Contact:	W 11	H 40	D 22
----------	------	------	------