



Lighting element for surface-mounted housing



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	1067 01	1/5	02	4010337105169
 pure white glossy	1067 03	1/5	02	4010337107088

Features

- The white LEDs project a light corridor downwards. This produces indirect orientation light that also avoids bothersome glare in bedrooms.

Technical data

Rated voltage:	AC 230 V, 50 Hz
Power consumption:	0.05 W / 1.65 mA
Light intensity:	0.2 cd
Ambient temperature:	0 °C to +40 °C