










**Gira Standard 55 cover frame with inscription space
pure white glossy**



| Specification | Order No. | Packing unit | PS | EAN |
|---|-----------|--------------|----|---------------|
|  1-gang | 1091 03 | 10 | 01 | 4010337091035 |
|  2-gang horizontal | 1092 03 | 10 | 01 | 4010337092032 |
|  2-gang vertical | 1102 03 | 10 | 01 | 4010337102038 |
|  3-gang horizontal | 1093 03 | 10 | 01 | 4010337093039 |
|  3-gang vertical | 1103 03 | 1/5 | 01 | 4010337103035 |
|  4-gang horizontal | 1094 03 | 1/5 | 01 | 4010337094036 |
|  4-gang vertical | 1114 03 | 1/5 | 01 | 4010337008910 |
|  5-gang horizontal | 1095 03 | 1/5 | 01 | 4010337095033 |
|  5-gang vertical | 1115 03 | 1/5 | 01 | 4010337115038 |

Features

- Shatter-proof.
 - Spray-proof.
 - Frames with transparent view window for inscription.
 - Ideally suited for use in buildings in which the electrical installation must be identified and documented, for example in administrations, commercial operations, airports, companies, and hospitals.
-

Notes

- Not to be used with: sealing kit IP44, surface-mounted housing with flat design, surface-mounted housing.
-