









SCHUKO socket outlet 16 A 250 V~ with LED orientation light and shutter



Specification	Order No.	Packing unit	PS	EAN
 cream white glossy	1170 01	1/5	02	4010337170013
 pure white glossy	1170 03	1/5	02	4010337170037
 pure white matt	1170 27	1/5	02	4010337170273
 anthracite	1170 28	1/5	02	4010337170280
 colour aluminium	1170 26	1/5	02	4010337170266
 black matt	1170 005	1/5	02	4010337037637
 grey matt	1170 015	1/5	02	4010337082903
 stainless steel (lacquered)	1170 600	1/5	02	4010337021124

Features

- SCHUKO socket outlet with inserted light strip.
 - The white LEDs project a light corridor downwards. This produces indirect orientation light that also avoids bothersome glare in bedrooms.
 - The integrated twilight sensor waits until twilight to automatically switch on the LED light and switches it off again when sufficient daylight is detected.
 - The LED light is completely integrated in the cover plate, eliminating the need for separate connection.
-

Technical data

Power consumption

- Operation: 0.25 W / 0.35 VA / 1.5 mA
- Standby: 0.175 W / 0.25 VA / 1.0 mA

Light intensity: 0.2 cd

Installation depth: 32 mm

Ambient temperature: -15 °C to +40 °C

Connections

- for conductors from: 1.5 mm² to 2.5 mm²
-

Notes

- Increased contact protection (Safety Plus) pursuant to IEC 60884-1.
-